

## **Showers & Eyewash**

Requirements specify that "... suitable facilities for quick drenching or flushing of the eyes and body shall be provided within the work area..."

Visit www.osha.gov for complete details and regulation requirements.





One of the top OSHA citations is lacking an emergency eyewash station. As required by law, protect employees and guard against personal injury claims. Operates with one motion, one hand. Gravity fed 15-minute flow time. No plumbing required. Provides a minimum 15-minutes flushing period. Includes mounting bracket, inspection tag and preservative. Change water every 3-6 months. Measures 11 1/2" x 19 1/2" x 25". Meets ANSI Z358.1.

ITEM #	ORDER #	DESCRIPTION	UOM
5135	G73551351	Portable eyewash station	Ea
5136	G7355136	Eyewash preservative, 8 oz.	4/Cs

#### Honeywell

#### Personal Eyewashes and Wall Stations

Sealed, sterile bottles contain Eyesaline<sup>®</sup> – a buffered, saline solution superior to tap water for emergency eye care. Blow-fill-seal bottles are tamper-resistant, yet easily removed in an emergency. Extended flow opening provides longer flow rate than conventional bottles. Durable, open face design holds bottles firmly in place with easy access to bottles in an emergency. Mounts to wall with provided screws. Durable plastic is easy-to-clean. Simple, highly visible operating instructions are provided on each unit. Bottles feature trilingual instructions. Ensured quality and



lasting value with FDA-grade polyethylene bottles featuring lot numbers and expiration dates. DOES NOT MEET the current ANSI Z358.1-2014 15-minute flushing requirement.

ITEM # ORDI	R # DESCRIP	TION	UOM
32-000460-0000 3415	01091 Single wa	all station, 16 oz. bottle	Ea
32-000461-0000 3415	01101 Single wa	all station, 32 oz. bottle	Ea
32-000465-0000 3415	6501 Double w	all station, 16 oz. bottles	4/Cs
32-000462-0000 3415	01111 Double w	all station, 32 oz. bottles	Ea





#### Honeywell

#### Fendall Pure Flow 1000<sup>®</sup> Eyewash Station

Saline is physiologically correct, buffered to the eye and delivered from factory-sealed cartridges. No costly plumbing required. Integral reservoir captures waste fluid. Stop valve allows easy draining of reservoir after use. Cartridges have 2-year shelf life; sold separately. Provides a constant ribbon fluid flow rate of 0.4 gpm for the entire 15-minute flushing period required by industry standards. Meets ANSI Z358.1-2014.



32-001050-0000

ORDER #	DESCRIPTION	UOM
341554681	Fendall Pure Flow 1000 eyewash station, English	Ea
341500791	Purified saline refill cartridges, trilingual	Pr
	341554681	341554681 Fendall Pure Flow 1000 eyewash station, English

32-001000-0000

#### Honeywell

#### Fendall 2000<sup>™</sup> Eyewash Station

Provides 100% sterile Eyesaline<sup>®</sup> eyewash solution via a 100% sterile delivery system. Portable unit includes emergency eyewash station sign, bracket, installation DVD and tamper seals. Integrated waste containment prevents spilling and empties easily. Built-in alarm sounds when unit is activated and again when 15-minute flush is complete. Measures 34 3/4" H x 17 1/2" W x 15 1/2" D. Sterile Eyesaline solution cartridges sold separately. 24-Month cartridge life. One-year warranty. Meets ANSI 2358.1-2014.

ITEM #	ORDER #	DESCRIPTION	UOM
32-002000-0000	341556331	Fendall 2000 eyewash station	Ea
32-ST2050-0000	341556341	Sterile Eyesaline refill cartridge	Ea

32-002000-000

EMERGENCY EYE

**ISH STATION** 

32-000100-0000



#### Honeywell

#### Fendall Porta Stream<sup>®</sup> I Eyewash Station

Portable, lightweight and delivers 6 minutes of uninterrupted, hands-free flushing without costly plumbing. Gravity-fed flow begins immediately when the nozzle pull strap is removed. Supplied with 70 oz. of Eyesaline® concentrate which, when mixed with tap water provides 6 gals. of saline solution. May be mounted on a wall, mobile cart or mobile stand for easy and affordable safety near most workplace hazards. Nozzle strap is easily removed, leaving hands free to hold eyelids open. Large fill hole simplifies refilling and cleaning. Illustrated operating instructions printed on the unit. Suitable for nuisance situations such as dust or particle flushing where a 15-minute flushing device is not a requirement. Hi-viz green.

#### ITEM # ORDER # DESCRIPTION

32-000100-0000 341500761 Fendall Porta Stream I eyewash station w/ saline concentrate

#### Honeywell

#### Fendall Porta Stream® II Eyewash Station

Portable, self-contained design may be mounted on a wall or mobile cart. Nozzle strap is easily removed to activate flushing, leaving hands free to hold eyelids open. Molded handle accepts hanging bracket for vertical or horizontal surface installation. Supplied with Eyesaline® concentrate; when mixed provides 14-16 gals. of preserved, buffered saline solution. Industry-compliant 15-minute flow cycle from a large 16-gal. reservoir permits thorough eye flushing by providing a 0.4 gpm flow rate over the eyes. Large fill hole with lockable fill cap simplifies refilling and cleaning and reduces risk of possible tampering. Includes Emergency Eyewash sign. Meets ANSI Z358.1-2014 15-minute flushing requirements for primary eyewash stations. Hi-viz green.

ITEM #	ORDER #	DESCRIPTION	UOM
32-000200-0000	341500881	Fendall Porta Stream II eyewash station w/ saline concentrate	Ea



UOM

Ea

Non-stock item. Minimum quantity may apply.

#### Honeywell

#### **Eyesaline® Personal Eyewashes**

Bottles contain Eyesaline saline solution for use in personal eyewash devices that offer secondary response and are intended to supplement, not replace, primary eyewash units. Also used for continued irrigation when moving an injured person from a primary eyewash unit to medical care. Easy-open top is tamper-resistant, yet easily removed in an emergency. User-controlled volume delivers drops or an irrigating stream of solution, depending on the squeeze pressure applied to the bottle. Made of FDA-grade polyethylene with lot numbers and expiration dates to ensure quality. Three-year shelf life.

ITEM #	ORDER #	DESCRIPTION	UOM
32-000451-0000	34150105	Eyesaline personal eyewash, 1 oz.	24/Cs
32-000454-0000	341501071	Eyesaline personal eyewash, 16 oz.	Ea
32-000455-0000	341501081	Eyesaline personal eyewash, 32 oz.	Ea

32-000454-0000

Protective Eyewear,	1
starting on Page 22.	



#### Honeywell

#### **Eyesaline<sup>®</sup> Concentrate**

Physiologically balanced to match natural tears and aid in reducing additional damage to the injured eye when flushed properly. Specifically formulated to be mixed with clean, potable water (10:1 ratio) and provides a cost-effective solution for the eyewash refills. May be used with Porta Stream<sup>®</sup> I, II & III (sold separately). The 180 oz. bottle makes 14-16 gals.; 70 oz. bottle makes 5-7 gals.

ITEM #	ORDER #	DESCRIPTION	UOM
32-000502-0000	341501141	Saline solution premix, 1 gal., for use w/ Fendall Porta Stream I, II & III	Ea
32-000509-0000	341501151	Saline concentrate, 70 oz., for use w/ Fendall Porta Stream I	Ea
32-000513-0000	341501171	Saline concentrate, 180 oz., for use w/ Fendall Porta Stream II & III	Ea



32-000513-0000



Guardian

#### G1100 EyeSafe<sup>™</sup> and G1101 EyeSafe-X<sup>™</sup> Faucet-Mounted Eyewashes

Features EyeSafe and EyeSafe-X mounts, easy installation and an unlimited supply of potable water for rinsing user's eyes. EyeSafe spray head outlets mount 3" apart to fit most faucets; EyeSafe-X large profile spray head outlets mount 5" apart to fit gooseneck faucets. Adjustable outlet heads deliver a soft, aerated flow of water. Includes forged brass diverter valve, inlet body with 55/64"-27 female thread and three adapters plus furnished outlet with removable aerator on bottom. Requires two motions to operate (turn on water, pull knob to activate eyewash flow). Intended solely as supplemental units for use with plumbed eyewash equipment already installed in the workplace. Should be used with cold or warm water only. Fully assembled and 100% tested.

ITEM # ORDER #	DESCRIPTION	UOM
G1100 B73101021	EyeSafe faucet-mounted eyewash	Ea
G1101 B73101031	EyeSafe-X faucet-mounted eyewash, gooseneck version	Ea

#### Guardian

### G1806 Deck-Mounted Eyewashes with 90° Swivel

Eyewash swings horizontally out over the sink for operation. Flow is activated with flag handle and remains in operation until handle is released. Two large GS-Plus<sup>™</sup> spray-type outlet heads deliver a flood of water for rinsing eyes. Each head has a "flip top" dust cover, internal flow control and filter to remove impurities. Polished chrome-plated brass construction. Meets ANSI Z358.1-2014 Classified Primary.

	ITEM #	ORDER #	DESCRIPTION	UOM
•	G1806	B73101981	Eyewash, deck-mounted, 90° swivel, right hand mount	Ea
•	G1806LH	B73101991	Eyewash, deck-mounted, 90° swivel, left hand mount	Ea





Self-contained, 16-gal. gravity-flow eyewash unit uses gravity to deliver water through dual spray heads. Unit delivers over 8 gals. (30 liters) of water for 15 minutes, thus complying with the provisions of ANSI Z358.1-2014 for eyewashes. Rugged plastic tank can be installed in a wide variety of locations. Ideal for use where a continuous supply of potable water is not available, especially in remote plant areas and low traffic areas. Tank has built-in carrying handle, heavy wall construction and reinforced ribs to support weight of unit. Eyewash delivers over .5 gallons per minute for 15 minutes. Water flow is activated by pulling down on bright yellow eyewash tray. Integral full flow nozzles deliver soft spray of water. Swing tray up to storage position to stop flow. Can be wall-mounted or used on countertop. Heated, freeze-resistant unit also available.

	ITEM #	ORDER #	DESCRIPTION	UOM
	G1540	B73101151	AquaGuard gravity-flow portable eyewash, 16 gal.	Ea
•	G1540HTR	B7311546	AquaGuard gravity-flow portable eyewash, heated	Ea
	G1540BA	B73101161	AquaGuard bacteriostatic additive, 8 oz.	Ea



#### Guardian G1600 Series Emergency Showers

ABS plastic shower head is 10" in diameter. Furnished with stainless steel actuating arm, 29" pull rod, and 1" IPS chrome-plated brass, stay-open ball valve with Teflon® seals. 1" NPT female inlet supply. 100% tested to meet ANSI Z358.1. Orange.

ITEM #	ORDER #	DESCRIPTION	UOM
♦ G1635	B73101271	Emergency shower, vertically mounted	Ea
♦ G1643	B73101311	Emergency shower, horizontally mounted	Ea









#### **G1814 Series Wall-Mounted Eyewashes**

Features (2) GS-Plus™ spray-type heads with "flip-top" dust cover, internal flow control and filter to remove impurities from the water flow. Includes signage and inspection tag. Fully assembled and 100% tested to meet ANSI Z358.1. Classified Primary.

ITEM #	ORDER #	DESCRIPTION	UOM	
G1814	B73102031	Eyewash w/ stainless steel bowl	Ea	
G1814P	B73102041	Eyewash w/ ABS plastic bowl	Ea	
G1814BC	B73111141	Eyewash w/ stainless steel bowl & cover	Ea	



#### **Guardian G1750 Series Eye/Face Washes**

Specially designed for wall mounting. Two large FS-Plus™ spray-type outlet heads deliver a flood of water for rinsing eyes and face. Spray head assembly features internal flow control and filter to remove impurities from the water flow. Furnished with 1/2" IPS chrome-plated brass, stay-open ball valve with Teflon® seals and 1/2" NPT female inlet supply. Heavy-duty cast aluminum wall bracket is corrosion-resistant with powder-coated finish. Includes ANSI-compliant identification sign. Fully assembled and 100% tested to meet ANSI Z358.1. Classified Primary.

ITEM #	ORDER #	DESCRIPTION	UOM
♦ G1750	B73101661	Eye/face wash, stainless steel bowl	Ea
+ G1750BC	B7310332	Eye/face wash, stainless steel bowl w/ cover	Ea
• G1750P	B73101671	Eye/face wash, plastic bowl	Ea

G1750P

G1750BC

#### **Guardian GFR3100 Heated Safety Station with Eyewash**

Electric heat-traced station prevents freezing even in extreme conditions. Thermostat regulated unit heated by self-limiting heat-tracing cable wrapped around internal pipe. Intended for cold weather use down to -40° F. Features 10" dia. orange ABS plastic shower head with 20 gpm flow control. Supplies are: 1 1/4" NPT female top supply inlet; 1" IPS brass stay-open ball shower valve with stainless steel actuating arm and 29" stainless steel pull rod; and 1/2" IPS brass three-way self-draining stay-open ball eyewash valve with 1/2" NPT port to drain water from spray heads after use. Valves made in USA with brass ball and Teflon® seals. Galvanized steel pipe and fittings, UV-resistant, orange, ABS plastic jacket with polyethylene foam insulation, and freeze-resistant spray head assembly with float-off dust covers and internal flow control. Units approved for Class I, Division 2, Groups B, C, and D. Electrical components are FM, UL® and CSA approved.

ITEM #	ORDER #	DESCRIPTION	UOM	GFR3100
GFR3100	B7313100	Heated safety station w/ eyewash	Ea	



#### Guardian

#### **G1902 Series Safety Stations with Eyewash**

Features 10" diameter, ABS plastic shower head and (2) GS-Plus<sup>™</sup> spray-type outlet heads with "flip-top" dust cover, internal flow control and filter to remove impurities. G1902BC eyewash has a stainless steel bowl and cover to protect spray heads from dust, dirt and other contaminants. Cover is raised automatically when flag handle is activated. Includes signage and inspection tags. 100% Tested to meet ANSI Z358.1.

	ITEM #	ORDER #	DESCRIPTION	UOM	
•	G1902	B7311903	Safety station eyewash & shower w/ stainless steel bowl	Ea	
•	G1902BC	B73103251	Safety station eyewash & shower w/ stainless steel bowl & cover	Ea	
•	G1902P	B7311902	Safety station eyewash & shower w/ plastic bowl	Ea	
					G1902



#### G1825 Series Pedestal-Mounted Eyewashes

Free-standing, pedestal-mounted eyewash. Two GS-Plus™ spray-type spray heads. Each head has a "flip top" dust cover, internal flow control and filter to remove impurities from the water flow. Water flow is activated by flag handle; optional bowl cover (on G1825BC model) is automatically raised when unit is activated. Includes ANSI-compliant identification sign. 100% Tested to meet ANSI Z358.1. Classified Primary.

	ITEM #	ORDER #	DESCRIPTION	UOM	
•	G1825P	B73102121	Eyewash, ABS plastic bowl	Ea	
•	G1825	B73102101	Eyewash, stainless steel bowl	Ea	
•	G1825BC	B7311825	Eyewash, stainless steel bowl & cover	Ea	

#### Guardian

G5026

Guardian

#### G5000 Series Eyewash/Drench **Hose Units**

Dual-purpose eyewash/drench hose for wall or deck mounting. Can be used as a fixed eyewash, leaving hands free. Unit may be removed for use as a drench hose to rinse any part of user's eyes, face or body. Fully assembled and 100% tested to meet ANSI Z358.1 as both an eyewash and a drench hose.

		ITEM #	ORDER #	DESCRIPTION	UOM	
7	•	G5026	B73102851	Eyewash/ drench hose unit, wall-mounted	Ea	
	•	G5022	B73102811	Eyewash/ drench hose unit, deck-mounted	Ea	

# 

G1825

#### G1562 15-Gal. Portable **Eyewash/Drench Hose Units**

Self-contained eyewash/drench hose units ideal for use where a continuous supply of potable water is not available, especially in remote plant areas, and low traffic areas where installation of plumbed equipment is not cost-effective. 15-Gal. units provide approximately 10 usable gals. (37.9 liters) of water for effective rinsing of the eyes, face or body, for fifteen minutes, thus complying with the provisions of ANSI Z358.1-2014 for eyewashes. Stainless steel pressurized tank includes built-in carrying handles, air intake fitting, pressure gauge and pressure relief valve. Unit features (2) GS-Plus™ spray heads, each with a "flip top" dust cover, internal flow control and filter, and a 1/2" IPS chrome-plated, brass stay-open ball valve with flag handle. Pressure regulator controls eyewash flow to 0.65 GPM for 15 minutes. Drench hose features single GS-Plus spray head with "flip top" dust cover, internal flow control and filter; chrome-plated, brass squeeze valve with stainless steel lever handle and 6' reinforced PVC hose. Heated, freeze-resistant model also available.

	ITEM #	ORDER #	DESCRIPTION	UOM
	G1562	B7311562	Portable eyewash/drench hose	Ea
•	G1562HTR	B7311547	Portable eyewash/drench hose, heated	Ea

# G1562



G1562HTR



#### Guardian G3600LF and G3800LF Tempering Valves

Blends hot and cold water by sensing incoming water temperature and automatically blending it to 85° F. High temperature limit stop is set to 90° F. Features dial thermometer on outlet to monitor temperature of delivered water. If hot water supply is restricted or fails, 20 gpm of cold water at 30 psi can be delivered. If cold water supply is lost, valve will close and not deliver water. 6-Gal. capacity valve has flow capacity of 2 to 6 gpm and can be used with eyewash, eye/face wash, dual purpose eyewash/drench hose and drench hose units. 44-Gal. capacity valve has flow capacity of 3 to 44 gpm and can be used with single installation of emergency showers and safety stations, and with multiple installations of emergency shower, eyewash, eye/face wash, dual purpose eyewash/drench hose, drench hose and safety station units.

	ITEM #	ORDER #	DESCRIPTION	UOM	
•	G3600LF	B73102541	G3600LF tempering valve, 6-gal. capacity	Ea	
٠	G3800LF	B73102621	G3800LF tempering valve, 44-gal. capacity	Ea	